CONDENSER		EVAPCO, INC. Evapco		DWG. # CEWR122412-DRA-ST	REV -
MODEL # PMRC-1004	NTS	EVAPCO, I		SERIAL#	DATE: 11/27/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.		FACE I	<u>sw</u>	ACE A	FACE D
3'-0 7/8" * [937]	5'-8 5/8" * [1743]		h		
O (4) 4" [100] PE O (4) 4" [100] PE	O — REFRIG IN O — REFRIG OUT	3'-11 3/4" [1213] * 7'-2 5/8" [2200]		
OVERSIZED ACCESS DOORS 3"[80] MPT 5 1/8" [130] MAKE UP 5 1/8" [130] 2'-5"[737]	Na No sor	9'-11" [3023] * 8'-6 3/8" [2600]		
1'-8" [508]	(2) 3"[80] MPT OVERFLOW	1'-7 1/8" [486	[7	0 7/8"	1'-6" [457]
1	1'-10 3/8" [3616]	_			
FACE B				FACE A	
SHIPPING WEIGHT 44420 lbs+ [20150] kg+	OPERATING WEIGHT	54650 lbs+ [24790] kg+	HEAVIEST SECTION 16860 lbs+ [7650] kg+	NO. OF SHIPPING SECTIONS	RAWN BY: JLG