CONDENSER	EVADCO 1	TNC evapco	DWG.# CEWR12C2412-DRB-ST	· -
MODEL # PMRC-1002 SCALE NT	EVAPCO, I	INC. evapeo	SERIAL#	re: 11/27/2025
NOTES:  1. (M)- FAN MOTOR LOCATION.  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.  6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE PLAN VI	B EW	ACE C	FACE D
3'-0 7/8" * 5'-8 5 [937]				
O (2) 4" [100] PE OVERSIZED ACCESS DOORS 3"[80] MPT DRAIN 2'-5"[737]	O			
1'-8" [508] - 4 3/4" [121] 3 7/8" [98] - 7'-4 3/8"	6]		<u>Е А</u>	
SHIPPING WEIGHT 44020 lbs+ [19970] kg+	OPERATING WEIGHT 54850 lbs+ [24880] kg+	HEAVIEST SECTION 33160 lbs+ [15045] kg+	NO. OF SHIPPING SECTIONS 2	' <sup>N BY:</sup> JLG