UNIT	COOLING TOWER	
MODEL #	AT 312-4M42	SCALE NTS

EVAPCO, INC. Evapco

DWG. # REV. T3124248-DRD-ST DATE_{12/13/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT **DRAWING**

29880 lbs+ [13555] kg+

WEIGHT

WEIGHT


7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


FACE C



FACE B

PLAN VIEW






FACE D

FACE A

6800 lbs+ [3085] kg+



WEIGHT

51870 lbs+ [23530] kg+