CONDENSER	EVADOO 1	TNIC evapco	DWG.# CEWR12C2412-DRB-ST	-
PMRC-1002 SCALE N	EVAPCO, 1	INC. evapeo	SERIAL # DATE:	12/13/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES SEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE PLAN VI	B EW	CE A	FACE D
3'-0 7/8" * 5'-8 5 [937]				
OVERSIZED ACCESS DOORS 3"[80] MPT 5 1/8" [130] 3"[80] MPT DRAIN 2'-5"[737]	4'-10 3/4" [1492] * 8'-0 5/8" [245			
1'-8" [508] - 4 3/4" [121] 3 7/8" [98] - 7'-4 3/8" 7'-4 3/8" 11'-10	6]	FACI	Ε Α	RV.
SHIPPING WEIGHT 44020 lbs+ [19970] kg+	OPERATING WEIGHT 54850 lbs+ [24880] kg+	HEAVIEST SECTION 33160 lbs+ [15045] kg+	NO. OF SHIPPING SECTIONS 2	BY: JLG