NIT				6	DWG.#	REV
ODEL#	CONDENSER	SCALE	EVAPCO, INC	evapco	CEWR121212-DRA-ST	- DATE:
ODEL#	PMRC-537	NTS	21711 00/ 2110		SENIAL #	11/27/2025
2. MPT DENG FPT DENG FPT DENG GVD DENG FLG DENG FLG DENG ACCESSO 4. 3/4" [19mn RECOMMI 5. MAKE-UP 50 psi [344 6. DIMENSIC ENGLISH [METRIC 7. * - APPRO		/INGS). ER TO VING. kPa] MIN,		FACE B PLAN VIEW	FACE A	FACE D
	3'-0 7/8" * [937]	5'-8 5/8" * [1743] O 4' [100] PE	REFRIG IN 3'-11 3/4" [1213] *	7'-2 5/8" [2200]		
		O 4" [100] PE R	O			
2"[50] MP1 MAKE UF 3"[80] DI 7 2'-5"[737]	P		15'-9" [4801] 9'-11" [3023] *	8'-6 3/8" [2600]		
1'-8" [508]-	3 7/8" [98] 4 3. 5'-0 3/8" [1534]	3/4" [121] 3/8"_ 11'-10 3/8"_ [3616]	3"[80] MPT OVERFLOW	1'-7 1/8" [486]	11'-11 3/4" [3651]	
		FACE B			FACE A	

HEAVIEST SECTION WEIGHT

16860 lbs+ [7650] kg+

SHIPPING WEIGHT

22610 lbs+ [10260] kg+

OPERATING WEIGHT

27590 lbs+ [12515] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG