NIT CONDENSER				DWG. #	REV -
ODEL#	NTS	EVAPCO,	INC. Evape	SERIAL#	DATE:
<b>_</b>	N15				11/27/2025
NOTES:  1. (M)- FAN MOTOR LOCATION.  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.  6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.			FACE B PLAN VIEW	FACE C	FACE D
				FACE A	
	4'-9" *				
(2) 4* [100] PE	REFRIG OUT	2'-6 3/4" [781] *	5'-9 5/8" [1768]		
<del>'                                    </del>		14'-4" [4369] 9'-11" [3023] *	8'-6 3/8" [2600]		
1'-8" [508] 4 3/4" [121] 3 7/8" [98] 5 1/8" [130] 3'-10 1/2" [1181]	3"[80] MPT OVERFLOW		1'-8" [508]		

HEAVIEST SECTION WEIGHT

15510 lbs+ [7040] kg+

**FACE A** 

DRAWN BY:

JLG

NO. OF SHIPPING SECTIONS

9'-9 3/4" [2991] **FACE B** 

23480 lbs+ [10655] kg+

SHIPPING WEIGHT OPERATING WEIGHT

29350 lbs+ [13315] kg+