UNIT CONDENSER		EVAPCO, INC. Evaped		DWG. # CEWRTM1812-DRA-ST	REV -
MODEL# PMRC-668 SCALE N	TS	EVAPCO, I	INC.	SERIAL#	DATE: 11/27/2025
NOTES:  1. (M)- FAN MOTOR LOCATION.  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAINE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.  6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.			FACE B PLAN VIEW	FACE C	FACE D
	9" * 448]  REFRIG IN  REFRIG OUT	3'-11 3/4" [1213] *	7'-2 5/8" [2200]		
OVERSIZED ACCESS DOORS  2"[50] MPT MAKE UP 3"[80] MPT DRAIN  2'-5"[737]	REPRICUOI	15'-9" [4801] 9'-11" [3023] *	8'-6 3/8" [2600]		
[29	3"[80] MPT OVERFLOW 0 3/4"		1'-8" [508]	18'-0 1/8" [5490]	
SHIPPING WEIGHT 28780 lbs+ [13055] kg+	OPERATING WEIGHT	34890 lbs+ [15830] kg+	HEAVIEST SECTION 21260 lbs+ [9645] kg+	FACE A  NO. OF SHIPPING SECTIONS  2	DRAWN BY: JLG