UNIT	COOLING TOWER	
MODEL #	AT 110-2J18	SCALE NTS

EVAPCO, INC. Evapeo




**FACE B** 

**PLAN VIEW** 

DWG. # REV. T3TM1824-DRD-ST DATE<sub>12/13/2025</sub> SERIAL #


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]






FACE D

**FACE A** 





DRAWN BY: KDS NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 9260 lbs+ [4205] kg+ 16860 lbs+ [7650] kg+ 5710 lbs+ [2595] kg+ WEIGHT WEIGHT WEIGHT