

UNIT	CONDENSER
MODEL #	eco-PMRC-959

EVAPCO, INC.



DWG. # CEWRTM3606-DRA-ST

REV -


SERIAL #

DATE: 2/19/2026

NOTES:


- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE B


PLAN VIEW



FACE A



FACE B



FACE A

SHIPPING
WEIGHT

45110 lbs+ [20465] kg+

OPERATING
WEIGHT

56930 lbs+ [25825] kg+

HEAVIEST SECTION
WEIGHT

15660 lbs+ [7105] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**