

UNIT	CONDENSER	
MODEL #	eco-PMRC-397	SCALE NTS


# EVAPCO, INC.




DWG. #	CEWR121204-DRA-ST	REV	-
SERIAL #		DATE:	2/20/2026

**NOTES:**


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B



**FACE B**



## FACE A

SHIPPING  
WEIGHT

15190 lbs+ [6895] kg+

## OPERATING WEIGHT

19790 lbs+ [8980] kg+

## HEAVIEST SECTION WEIGHT

9480 lbs+ [4305] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: **JLG**