

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. #	WB3171212-DRD-ST	REV.	-
MODEL #	ATWB 17-6L12	SCALE	NTS		SERIAL #		DATE	3/14/2026
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]					FACE C (M) (2) ACCESS DOOR FACE D FACE B PLAN VIEW FACE A (4) 1/2" [15] FPT VENT			
1'-9 3/8" [543] 3'-6" [1067] 1'-11 1/8" [589] 3" [76] 4'-3/4" [1238] 2'-2 3/8" [670] 8'-10" [2694] 13'-10 1/4" [4223] 6" [154] 5'-1/4" [1529] 2'-10 1/4" [870] 1'-3" [383] 8'-1/4" [2445] 8'-1 1/4" [2470] 8'-5 1/2" [2578] 5 1/8" [130] 17'-4 1/8" [5286] FACE B 1'-7/8" [327] 11'-11 3/4" [3651] 1'-3 5/8" [397] FACE A					SHIPPING WEIGHT 29920 lbs+ [13575] kg+ OPERATING WEIGHT 44160 lbs+ [20035] kg+ HEAVIEST SECTION WEIGHT 13160 lbs+ [5970] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR			