UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 17-7K14


EVAPCO, INC. Evapco





DWG. # REV. WB3171414-DRD-ST DATE 11/18/2025 SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







SHIPPING WEIGHT

38500 lbs+ [17465] kg+

OPERATING WEIGHT

56380 lbs+ [25575] kg+

HEAVIEST SECTION WEIGHT

17240 lbs+ [7820] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR