


UNIT		CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div></div>	DWG. #	WB3171414-DRD-ST	REV.	-
MODEL #	ATWB 17-7M14	SCALE	NTS		SERIAL #		DATE	7/14/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.


8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW




FACE B

FACE C

FACE D

FACE A



FACE A

SHIPPING WEIGHT	38660 lbs+ [17540] kg+	OPERATING WEIGHT	56540 lbs+ [25650] kg+	HEAVIEST SECTION WEIGHT	17320 lbs+ [7860] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	SLR
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----