

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #


U-EJETME3-2883F0033F1KA

N.T.S.

UEJETM3-SE-16,18

REV. 0


DATE	11/22/2025
------	------------



- NEMA 4X
JUNCTION BOX

NOTES:

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



Technical drawing of a vertical riser assembly. The drawing shows a cross-section of the assembly with various dimensions and labels. The top dimension is 45 3/8. Below it, the distance from the left wall to the center of the riser is 41 3/8, with a 3/4 inch offset on each side. The riser has a height of 57 1/2 inches. The distance from the top of the riser to the top of the horizontal section is 9 1/4 inches. The total height of the assembly is 62 3/4 inches. The horizontal section has a width of 55 inches, with 1 1/4 inch offsets on each side. The total width of the assembly is 57 1/2 inches. Labels include "AIR FLOW" with an arrow pointing left, "2" MPT DRAIN", and "BOX". Dimensions are given in feet and inches.

ROOM

SHIPPING
WEIGHT

1280 lbs+ [585] kg+

OPERATING WEIGHT	10000
------------------	-------

1500 lbs+ [685] kg+