

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-EJETME2-19103F0075F3KA
---------	--------------------------

DWG. # UEJETM2-SE-16,18

DATE	9/13/2025
------	-----------



Technical drawing of the front view of a device. The drawing shows two circular fans with a radial grille pattern. To the right of the fans is a rectangular control panel with a small rectangular button or indicator. Dimension lines indicate the following measurements:

- Total width: $126 \frac{3}{8}$
- Distance from left edge to first fan center: 6
- Distance between fan centers: 42 (indicated by two arrows, each labeled 42)
- Distance from second fan center to right edge: $36 \frac{3}{8}$
- Distance from left edge to first fan center (bottom): 4
- Distance between fan centers (bottom): 42 (indicated by two arrows, each labeled 42)
- Distance from second fan center to right edge (bottom): $38 \frac{5}{8}$

Technical drawing of a mechanical part with dimensions and labels:

- Overall width: $45 \frac{3}{8}$
- Top horizontal dimensions: $\frac{3}{4}$, $* 41 \frac{3}{8}$, $\frac{3}{4}$
- Right side vertical dimensions: $4 \frac{7}{8}$, $** 7 \frac{1}{4}$, $54 \frac{5}{8}$, $60 \frac{3}{4}$
- Bottom horizontal dimensions: $\frac{1}{4}$, 55 , $1 \frac{1}{4}$, $57 \frac{1}{2}$
- Labels: AIR FLOW (with arrow), PT IN

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.

ROOM

1070 lbs+ [490] kg+

1260 lbs+ [575] kg+