

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #

SCALE

DWG. #

REV. 0

DATE	9/15/2025
------	-----------



- NEMA 4X
JUNCTION BOX



Technical drawing of the front view of a mechanical part. The drawing includes the following dimensions and features:

- Overall width: $45 \frac{3}{8}$
- Top horizontal dimensions: $\frac{3}{4}$, $* 41 \frac{3}{8}$, and $\frac{3}{4}$.
- Right side vertical dimensions: $4 \frac{7}{8}$, $** 7 \frac{1}{4}$, $54 \frac{5}{8}$, and $60 \frac{3}{4}$.
- Bottom horizontal dimensions: 4 , 55 , and $1 \frac{1}{4}$.
- Overall bottom width: $57 \frac{1}{2}$.
- Internal features: A vertical slot on the left, a small square hole, a small circle, and a larger circle.
- Text: "AIR" and "LOW" with a wavy line symbol on the left side.

NOTES:

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.

ROOM

SHIPPING WEIGHT

1090 lbs+ [495] kg+

OPERATING WEIGHT	10000
------------------	-------

1260 lbs+ [575] kg+