NOTES: 1. (M)- FAN MOTOR LOCATIO 2. HEAVIEST SECTION IS UPI 3. MPT DENOTES MALE PIPE FPT DENOTES FEMALE PIFE BFW DENOTES BEVELED I GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT ACCESSORIES (SEE ACCE	PER SECTION THREAD PE THREAD	EVAPC	O, INC.	evapco	SERIAL #	DATE _{12/13/2025}
(M)- FAN MOTOR LOCATIO HEAVIEST SECTION IS UPI MPT DENOTES MALE PIPE FPT DENOTES FEMALE PII BFW DENOTES BEVELED I GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT ACCESSORIES (SEE ACCE	PER SECTION THREAD PE THREAD			<u> </u>	FACE C	•
5. MAKE-UP WATER PRESSU 20 psi MIN [137 kPa], 50 psi 6. *-APPROXIMATE DIMENSIC FOR PRE-FABRICATION OF PIPING 7. 3/4" [19mm] DIA. MOUNTING RECOMMENDED STEEL SU 8. DIMENSIONS LISTED AS FOR ENGLISH FT-IN METRIC [mm]	SSORY DRAWINGS) RE MAX [344 kPa] DNS DO NOT USE CONNECTING GHOLES. REFER TO DPPORT DRAWING.		FACE B PLAN VIEW		R ACCESS DOOR	FACE D
ĪĆ		7" [178]	1'-3 1/4' [387]			
2'-6 3/4" * [781]	5'-9 1/4" *	3'-3/8" * [924] 9'-1/8" [2748] 15'-2 3/8	3"		M)	
(2) 2" [50] MPT — MAKE-UP 2'-1 1/4" [643]		6" * 6'-2 1/4" [1884]				
3 5/8" DRAI [92] - 5 1 - 5 1 1	1/4" 33] 1/4" 08]	1'-5" [433] -(2) 3" [80] MPT OVERFLOW		11'-11 3/4"	2 1/2" [64]	
[7'-2" 2184] ————————————————————————————————————		1'-4 3/4" [425]		24'-2" [7366]	1'-4 3/4" [425]