NIT CONDENSER				DWG. # WB3243610-DRC-ST	REV.	
MODEL #	ATC-2900E	SCALE NTS	EVAPCO,	INC. evapeo	SERIAL #	DATE _{10/30/2025}
2. HEAVIES 3. MPT DEI FPT DEI BFW DE GVD DEI FLG DEN PE DEN(4. +UNIT W ACCESS 5. MAKE-UI 20 psi MI 6. *APPRO FOR PRI PIPING 7. 3/4" [19m RECOMM	I MOTOR LOCATION ST SECTION IS UPPER SE NOTES MALE PIPE THREA NOTES FEMALE PIPE THR NOTES GROOVED NOTES GROOVED NOTES FLANGE DTES PLAIN END /EIGHT DOES NOT INCLUI SORIES (SEE ACCESSORY P WATER PRESSURE IN [137 KPa], 50 psi MAX [3 DXIMATE DIMENSIONS DO E-FABRICATION OF CONN nm] DIA. MOUNTING HOLE MENDED STEEL SUPPOR IONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD JEAD ELDING DE TORAWINGS) 44 kPa] DNOT USE JECTING ES. REFER TO T DRAWING.	PLAN	FACE B VIEW	FACE A (4) ACCESS DOOR (5) (4) (4) (5) (6) (7) (7) (8) (8) (9) (9) (9) (9) (10)	FACE D
2'-1 1/4" [643] 1'-5' [433	(8) 4" [100] PE (EF) (9) 1 (1) 2" [50] MAK (4) 3" [80] 92]	MPT 11'-4	9'-8 5/8" [2964]	1'-3 1/4" (387) (0) (0) (1) (1) (1) (1) (1) (1) (1) (1) (1) (1	1'-11 1/8" [587]	

FACE B

FACE A