NIT CONDENSER	EVADOO TNO EVODOO	DWG. # CW4C071208-DRA-ST REV
ODEL # ATC-282E SCALE NTS	EVAPCO, INC. evapeo	SERIAL # DATE <sub>10/30/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS FAN/CASING SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING  7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	FACE B PLAN VIEW	FACE D  FACE A
1'-9 3/8" [ 543 ] 3'-6 1/4" *	2'-11 3/8" [ 899 ] 1'-10 7/8" * 4'-8 3/8" [ 1432 ]	
2" [50] MPT —	- 5 1/4" * 4'-3 7/8"	
107   4 1/4"   107   1	-3" [80] MPT OVERFLOW 1'-5 1/8" [ 435 ] IG 12820 lbs+ [5820] kg+ HEAVIEST SECTION 8770 lbs+ [3980]	11'-11 3/4" [ 3651 ] FACE A  D] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TAM