UNIT CONDENSER			EVAPCO, INC. Evapco				DWG. # CW4C071810-DRA-ST	. REV
10DEL #	ATC-441E	SCALE NTS	- EVAP	CO, .	INC.	Evaseo	SERIAL #	DATE 11/4/2025
2. HEAVIES 3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENC 4. +UNIT WI ACCESS 5. MAKE-UF 20 psi MII 6. *-APPRO FOR PRE PIPING 7. 3/4" [19m RECOMM 8. DIMENSIO	MOTOR LOCATION T SECTION IS FAN/CASIN OTES MALE PIPE THREA OTES FEMALE PIPE THREA OTES GROOVED OTES GROOVED OTES FLANGE TES PLAIN END EIGHT DOES NOT INCLUE DRIES (SEE ACCESSORY WATER PRESSURE N [137 kPa], 50 psi MAX [34 KIMATE DIMENSIONS DO -FABRICATION OF CONNI m] DIA. MOUNTING HOLE: ENDED STEEL SUPPORT DNS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	D EAD ELDING  DE DRAWINGS)  14 kPa] NOT USE ECTING  S. REFER TO DRAWING.		<u>PLAN</u>	FACE B VIEW	ACCESS DO	FACE A	FACE D
2" [50] MF MAKE-U 2" [50] MF DRAI 1'-11 1 [ 587 <u>†</u> 3" [ 76	P T N V8"	REFRIG OUT	2'-11 3/8" [899]  1'-10 7/8" *  5'-3 7/8" [1622]  13'-3 1/2" [4051]  5'-1/4" [1530]  1'-3" [381]  -3" [80] MPT OVERFLOW	11.	11-2" [ 356 ]		[18'-0"] [5486]  FACE A	
SHIPPING WEIGHT	18210 lbs+ [826	60] kg+	OPERATING 21620 lbs+ [98	810] kg+	HEAVIEST SECT WEIGHT	TON 15190 lbs+ [6895] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: TAM