UNIT CONDENSED			1		ſ		•	DWG. #			REV.
CONDENSER		_	/APCO,	TNC	evo	ip c o		CW4C071812-DF	KA-ST	-	
MODEL #	ATC-422E	SCALE NTS	- 1	APCO,	TITC			SERIAL #			DATE 11/4/2025
2. HEAVIES 3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENC 4. +UNIT W ACCESS 5. MAKE-UF 20 psi MII 6. *-APPRO FOR PRE PIPING 7. 3/4" [19m RECOMM 8. DIMENSI	MOTOR LOCATION T SECTION IS FAN/CASIN IOTES MALE PIPE THREA OTES FEMALE PIPE THREA IOTES BEVELED FOR WE IOTES GROOVED OTES FLANGE DIES PLAIN END EIGHT DOES NOT INCLUI ORIES (SEE ACCESSORY WATER PRESSURE N [137 KPa], 50 psi MAX [3: XIMATE DIMENSIONS DO EFABRICATION OF CONN m] DIA. MOUNTING HOLE IENDED STEEL SUPPOR ONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	DE DRAWINGS) 44 kPa] NOT USE JECTING S. REFER TO DRAWING.		PLA	FACE B		ACCESS D	FACE A		ACCESS DOC	FACE D
2" [50] M MAKE- 2" [50] M DRA 1'-11 1 1 587 1 3	UP PT IN	REFRIG OUT	2'-11 3/3 [899] 1'-10 7/8" *	8" 13'-11" 4242]	1'-2" [356 1'-47/8" [429]			18'-0" 5486 FACE A			
SHIPPING 20350 lbc. [0235] kg.		OPERATING 2	23850 lbs+ [10820] kg+	HEAVIEST SEC	TION	17330 lbs+ [7865] kg+		OF SHIPPING SECTIONS	2 DRA	WN BY: TAM	
WEIGHT	_5555 .55 . [626		WEIGHT 2		WEIGHT		211 [, 000]g.				17 11 1