UNIT CLOSED CIRCUIT COOLER MODEL # ATWB 24-6N14 SCALE NTS EVAPCO, INC.						apco	DWG. #	WB3241412-DRC-ST	REV.	
MODEL #	ATWB 24-6N14	SCALE NTS	TEVAP	JO, 11	VC.	1	SERIAL #		DATE 11/8/2025	
2. HÉAVIES 3. MPT DEN FPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENO 4. +UNIT WE ACCESSO 5. MAKE-UP 20 psi MIN 6. *-APPRO FOR PRE- PIPING 7. 3/4" [19mr RECOMM 8. DIMENSIO	MOTOR LOCATION I SECTION IS UPPEI OTES MALE PIPE THOTES FEMALE PIPE OTES FEMALE PIPE OTES GROOVED OTES FLANGE TES PLAIN END EIGHT DOES NOT IN DRIES (SEE ACCESS WATER PRESSURE I [137 kPa], 50 psi MA I [137 k	HREAD THREAD R WELDING CLUDE GORY DRAWINGS) E AX [344 kPa] S DO NOT USE CONNECTING HOLES. REFER TO PORT DRAWING.			<u>P</u>	FACE B			CE D	
l		_			7" [178]	1'-3 1/4" [387]	<u>F/</u>	ACE A		
	3'-11 3/4" *	(4) 4" [100] BFW FLUID OI (4) 4" [100] BFW FLUID OI (2) 2" [50] MPT MAKE-UF (2) 3" [80] M DRA 5 1/8	11'-4 3/4" [3473] 11'-5 3/4" [3499]	6" * [4'-8" [1422]	10'-5 1/8" [3180] 17'-7 3/8 [5369] 7'-2 1/4" [2189]	(4) 1/2" [15] FPT VENT	★			
	-		24'-1 1/8"			1'-6 1/2"		-11 3/4"		
	FACE B									
SHIPPING WEIGHT	49200 lbs+	[22320] kg+	OPERATING 75140 lbs+ [340)85] kg+	HEAVIEST SECTION WEIGHT	21540 lbs+ [9775] kg+	NO. OF	SHIPPING SECTIONS 4	DRAWN BY: SLR	