CONDENSER		EVADCO 1		/apco °	DWG.# CW4C141408-DRB-ST	REV -
ODEL# ATC-591E SCALE N	TS	EVAPCO, 1	LINC.		SERIAL#	DATE: 11/5/2025
NOTES  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS FAN/CASING SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAW)  5. MAKE-UP WATER PRESSURE  20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  6. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING  7. 3/4" [19mm] DIA. MOUNTING HOLES. REFE RECOMMENDED STEEL SUPPORT DRAW  8. DIMENSIONS LISTED AS FOLLOWS:  ENGLISH FT-IN METRIC [mm]	NGS) SE R TO		FAC PLAN	VIEW O	FACE C (M) ACCESS DOOR CESS DOOR (M)	FACE D
1'-9 3/8" [543]  2'-3" [686]  (M)  2'-3" [686]  (a) 4" [100] PE  (c) 4" [100] PE  (d) 4" [100] PE  (e) 4" [100] PE  (e) 4" [100] PE  (f) 4" [100] PE  (g) 4" [100] PE  (h) 4" [100] PE  (l) 4" [1	(4) 4'   100  PE REFRIG IN (4) 4'   100  PE REFRIG IN (2) 2" [50] MPT MAKE-UP (2) 2" [50] MPT DRAIN  5 1/8" [130]	1'-10 7/8" * [581]  2'-11 3/8" [899]  (M)  4'-8 3/8" [1432]  13'-2" [40  5 1/4" [133]  5'-6 1/4" [1683]  -1'-3" [381]  (2) 3" [80] MPT  OVERFLOW	12]	1'-2" [355]	ACCESS ACCESS DOOR	
FACE  SHIPPING WEIGHT 24360 lbs+ [11050] kg+		26110 lbs+ [11845] kg+	HEAVIEST SECTION WEIGHT	9990 lbs+ [4535] kg+	FACE A  NO. OF SHIPPING SECTIONS  4	DRAWN BY: JLG