NIT COLUMNIT					» D\	NG.#	REV
CONDENSER		EVAPCO,	TNC	evapco		CW4C141412-DRB-ST	-
ATC-748E SCALE N	rs	LVAPCO	<b>111C</b> .		SE	ERIAL #	DATE: 11/4/2025
NOTES  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS FAN/CASING SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAINE END  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINDS MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING  7. 3/4" [19mm] DIA. MOUNTING HOLES. REFEIRECOMMENDED STEEL SUPPORT DRAWING BOLISH FT-IN METRIC [mm]	NGS) E R TO		<u>F</u>	FACE B	Q CES	FACE C  (M)  ACCESS DOOR  S DOOR  (M)  FACE A	FACE D
[2235]	(a) 4" [100] PE	1'-10 7/8" * [581]  2'-11 3/8" [899]  5'-11 3/8" [1813] 14'-5" [4  5 1/4" [133] * 5'-6 1/4" [1683]  1'-3" [381] (2) 3" [80] MPT OVERFLOW	393]		2" [355]	FACE A  13'-11 3/4" [4261]	
FACE		22420 lba - [45005] bar	HEAVIEST SECTION	12000 11 10	0001 km	NO OF SHIPPING SECTIONS	DRAWN BY: JLG
SHIPPING 31100 lbs+ [14110] kg+	OPERATING WEIGHT	33120 lbs+ [15025] kg+	HEAVIEST SECTION WEIGHT	13360 lbs+ [6	060] kg+	NO. OF SHIFFING SECTIONS 4	JLG