

UNIT		COOLING TOWER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	T3TM1224-DRD-ST	REV.	-
MODEL #		AT 110-2M12			SCALE	NTS		SERIAL #
								12/13/2025
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE</div> <div> ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO</div> <div> RECOMENDED STEEL SUPPORT DRAWING.</div> <div>7. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> [METRIC] [mm]</div>								
<div><div>FACE B</div><div>PLAN VIEW</div></div>					<div><div>FACE C</div><div>ACCESS DOOR</div><div>FACE D</div><div>FACE A</div></div>			
<div><div>FACE B</div><div>Diagram of Face B with dimensions: 7" [178], 8'-3" [2515], 2" [51], 13'-5 1/4" [4096], 5'-2 1/4" [1581], 9'-9 3/4" [2991], 3/8" [9]</div></div>					<div><div>FACE A</div><div>Diagram of Face A with dimensions: 1'-3 1/4" [387], 5'-11 7/8" [1826], 8'-1" [2464], 2" [50] MPT MAKE-UP, 8" [200] BFW/GVD INLET, 3" [80] FPT OVERFLOW, 3" [80] FPT DRAIN, 8" [200] BFW/GVD OUTLET, 2'-1 1/4" [641], 1'-4 7/8" [429], 7 1/4" [184], 3 5/8" [92], 5 1/4" [133], 9" [229], 5'-11 7/8" [1826], 11'-11 3/4" [3651]</div></div>			
SHIPPING WEIGHT		6890 lbs+ [3130] kg+		OPERATING WEIGHT	11850 lbs+ [5380] kg+		HEAVIEST SECTION WEIGHT	4470 lbs+ [2030] kg+
NO. OF SHIPPING SECTIONS		2		DRAWN BY:		JLG		