


UNIT <b>COOLING TOWER</b>		<b>EVAPCO, INC.</b> 	DWG. # T3040424-DRJ-ST	REV. -
MODEL # AT 14-2E4	SCALE NTS		SERIAL #	DATE 7/18/2025


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]

**FACE B**

**PLAN VIEW**




**FACE C**


ACCESS DOOR

**FACE D**

**FACE A**





**FACE B**

SHIPPING WEIGHT

1080 lbs+ [490] kg+

OPERATING WEIGHT

1710 lbs+ [780] kg+

HEAVIEST SECTION WEIGHT

730 lbs+ [335] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

KWC