


UNIT		COOLING TOWER		<div>EVAPCO, INC.</div> <div></div>	DWG. #	T3041224-DRJ-ST	REV.	-	
MODEL #		AT 14-2F12			SCALE	NTS		SERIAL #	DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.

7. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-3/4" [324]

(M)

2'-1/8" [613]

6" [150] MPT INLET

6" [150] MPT OUTLET

1" [25] MPT MAKE-UP

5 7/8" [149]

2" [50] MPT OVERFLOW

2" [50] MPT DRAIN

3'-1 1/2" [953]

1'-7 3/4" [502]

10 1/4" [260]

2'-1/4" [616]

4'-1/2" [1232]

4 3/8" [111]

5 1/8" [130]

3" [76]

1'-1" [330]

9'-6 1/2" [2908]

6'-5" [1956]

FACE B

1'-1" [330]

3 1/8" [79]

6'-3" [1905]

11'-11 3/4" [3651]

FACE A

SHIPPING WEIGHT	2530 lbs+ [1150] kg+	OPERATING WEIGHT	4650 lbs+ [2110] kg+	HEAVIEST SECTION WEIGHT	1770 lbs+ [805] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	KWC
-----------------	----------------------	------------------	----------------------	-------------------------	---------------------	--------------------------	---	-----------	-----