UNIT COOLING TOWER		WER
MODEL #	AT 14-2G12	SCALE NTS

EVAPCO, INC. Evapeo


DWG. # T3041224-DRJ-ST REV.
SERIAL # DATE_11/12/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]





PLAN VIEW



FACE D

FACE A





SHIPPING WEIGHT 2570 lbs+ [1170] kg+ OPERATING WEIGHT 4690 lbs+ [2130] kg+ HEAVIEST SECTION WEIGHT 1810 lbs+ [825] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: KWC