NIT	COOLING TOWER		VAPCO, I	NC E	evapco	DWG. #	T4142660-DRA-ST	REV
ODEL #	AT 114-5L26 SCALE N	rs 🖿	VAPCO, I			SERIAL #		DATE 11/12/2025
2. HEAV 3. MPT I FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. 3/4" [1 REFEI DRAW 7. DIMM EN	AN MOTOR LOCATION IEST SECTION IS UPPER SECTION DENOTES MALE PIPE THREAD DENOTES BEVELED FOR WELDING DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END 'WEIGHT DOES NOT INCLUDE SSORIES (SEE ACCESSORY DRAWINGSUP WATER PRESSURE MIN [137 kPa], 50 psi MAX [344 kPa] 9MM] DIA. MOUNTING HOLES. R TO RECOMMENDED STEEL SUPPORT //ING NSIONS LISTED AS FOLLOWS: NGLISH FT-IN		<u>PL</u>	FACE B AN VIEW			2) ACCESS DOOR	ACE D
IM	ETRIC] [mm]	7" [178]		1'-3 1/4" [387]	<u>FA</u>	CE A		
		12'-1/4" [3664] - [51] 22'-3 [67'	1/2" 94] 16'-3 3/4" [4972]		12'-10 1/2" [3923] 12'-10 1/2" [3923] 4" [100] FPT OVERFLOW 4" [100] FPT DRAIN A" [100] FPT DRAIN	INLE	[350] BFW/GVD S350] BFW/GVD ET	
	13'-11 1/4" [4248]	3/8" [9]	1'-5 3/8" [441] 9" [229] 4 1/8" [105] .	9" [229] 6'-6 1/4" [1988]	12'-10 1/2" [3924] 2	5'-9" 7849]		
FACE B							CLUDDING SECTIONS	DD AWAL DV.
SHIPPING WEIGHT	24860 lbs+ [11280] kg+	OPERATING WEIGHT	41530 lbs+ [18840] kg+	HEAVIEST SECTION WEIGHT	17720 lbs+ [8040] kg+	NO. OF S	SHIPPING SECTIONS 2	DRAWN BY: MER