JNIT COOLING TOWER			EVAPCO, INC. evapco				G. # T414	REV	
IODEL #	AT 214-5O52	SCALE NTS	EVAP	CO, INC		SER	IAL #		DATE <sub>11/22/2025</sub>
2. HÉAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT 20 psi N 6. 3/4" [19 REFER DRAWI 7. DIMEN:	N MOTOR LOCATION EST SECTION IS UPPER SE ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WI ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUI SORIES (SEE ACCESSORY JP WATER PRESSURE AIN [137 kPa], 50 psi MAX [3 MM] DIA. MOUNTING HOLE TO RECOMMENDED STEE NG SIONS LISTED AS FOLLOW GLISH FT-IN TRIC] [mm]	AD READ ELDING  DE Y DRAWINGS)  A44 kPa] ES. EL SUPPORT	FACE B PLAN VIEW		(2) ACCESS DOOR	ACE C		(2) ACCESS DOOR	FACE D
		7" [ 178 ]	1'-3 1/4" [ 387 ]						
		12'-1/4" 2" [ 3664 ] [ 51 ]	1/2"	12'-10 1/2" [ 3923 ]			m ] Q	(2) 14" [350] BFW/GVD INLET	
		10'-3 1/4" [ 3131 ]	16'-3 3/4" [ 4972 ]				-(2) 3" [80] MPT	—(2) 14" [350]	
	13'-11 1/4" [4248]	← 3/8" [9]	2'-2" [ 660 ] 1'-5 3/8" [ 441 ] 9" [ 229 ] 4 1/8" [ 105 ]	12'-10 1/2"	9" 9 ]	(2) 4" [100] FP' OVERFLOW (2) 4" [100] FP' DRAIN (2) 4" [100] FP' DRAIN (3) 4" [100] FP' DRAIN (4) 11-8 1/2" (5) 11-8 1/2"	MAKE-UP T	BFW/GVD OUTLET	
ı	[ 4248 ] FACE B	[9]	,-			15761 ] <b>ACE A</b>			•
SHIPPING			PERATING 83500 lbs. I	1378751 kg.t HEAVIE			NO. OF SHIPPING		DRAWN BY: MER