UNIT	COOLING TOWER	
MODEL #	AT 314-21 72	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # REV. T4147224-DRA-ST DATE_{11/14/2025} SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED**


FLG DENOTES FLANGE PE DENOTES PLAIN END

- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT **DRAWING**
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]









FACE D

7" [178] 9'-2 1/4" [2800] -(3) 14" [350] 2" 51] 11'-10 1/2" [3620] BFW/GVD 17'-5 1/2" [5321] 11'-3 3/4' [3448] 8'-3 1/4" [2521] --(3) 3" [80] MPT MAKE-UP (3) 14" [350] 2'-2" [660] BFW/GVD 1'-5 3/8" [441] -(3) 4" [100] FPT OVERFLOW 9" [229] -(3) 4" [100] FPT DRAIN 23'-0" [7010] 4 1/8" [105] 23'-9" [7239] 71'-8" [21844] **FACE B FACE A**

10650 lbs+ [4835] kg+