| UNIT | COOLING TOWER | | |
|---------|---------------|-----------|--|
| MODEL # | AT 112-2K14 | SCALE NTS | |

EVAPCO, INC. Evapco

| OWG. # | T3121424-DRE-ST | REV |
|----------|-----------------|----------------------------|
| SERIAL # | | DATE _{12/14/2025} |

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]






FACE D

FACE A





 SHIPPING WEIGHT
 8360 lbs+ [3795] kg+
 OPERATING WEIGHT
 15690 lbs+ [7120] kg+
 HEAVIEST SECTION WEIGHT
 5490 lbs+ [2495] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY: KDS