UNIT	COOLING TOWER		
MODEL #	AT 212-4I28	SCALE NTS	

EVAPCO, INC. EVAPCO


DWG. #	T3122848-DRE-ST	REV.
SERIAL #		DATE _{11/21/202}

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]


FACE C


FACE B



FACE D

FACE A





SHIPPING WEIGHT 19180 lbs+ [8700] kg+ OPERATING WEIGHT 33840 lbs+ [15350] kg+ HEAVIEST SECTION WEIGHT 6540 lbs+ [2970] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: KDS