UNIT COOLING TOWER

MODEL # AT 224-3O20 SCALE NTS


EVAPCO, INC. Evapeo

DWG. # T3242036-DRC-ST REV. SERIAL # DATE_{11/21/2025}

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]






FACE D

FACE A





SHIPPING WEIGHT 26080 lbs+ [11830] kg+ OPERATING WEIGHT 46880 lbs+ [21265] kg+ HEAVIEST SECTION WEIGHT 8420 lbs+ [3820] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: BLL