UNIT	COOLING TOWER	
MODEL #	AT 424-3N40	SCALE NTS

EVAPCO, INC. Evapeo




DWG. # REV. T3244036-DRC-ST DATE 11/6/2025 SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


FACE C



FACE D

FACE A





DRAWN BY: BLL NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 51440 lbs+ [23335] kg+ 92640 lbs+ [42025] kg+ 9000 lbs+ [4085] kg+ WEIGHT WEIGHT WEIGHT