UNIT	CLOSED CIRCUIT CO	OLER	EVAPCO, INC. Evapeo		DWG. # WB3TM2412-DRC-ST	REV.
MODEL #	ATWB 10-6M24	SCALE NTS	EVAPC	O, INC.	SERIAL #	DATE <sub>12/14/2025</sub>
2. HEAVI 3. MPT D FPT DI BFW C GVD D FLG DI PE DE 4. +UNIT ACCES 5. MAKE- 20 psi   6. *-APPF FOR P PIPINC 7. 3/4" [18 RECOI	AN MOTOR LOCATION IEST SECTION IS UPPER SEDENOTES MALE PIPE THREAD ENOTES FEMALE PIPE THREAD ENOTES BEVELED FOR WEDENOTES FLANGE INOTES PLAIN END WEIGHT DOES NOT INCLUE SSORIES (SEE ACCESSORY-UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DOPRE-FABRICATION OF CONNICTORY OF CONNICTORY OF CONSIDERATION OF CONSIDERATION OF CONSIDERATION OF CONSIDERATION STEEL SUPPORT ASSONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	DE DRAWINGS)  44 kPa] NOT USE ECTING  S. REFER TO DRAWING.		FACE B PLAN VIEW	FACE C SS DOOR  ACCESS DOOR  FACE A	FACE D
			7" [ 178]			
<u> </u>	3'-11 3/4" * (4) 4" [100] BFW  2" [50] MPT	FLUID IN	2'-6 3/8" * [ 772] *  10'-5 1/8" [ 3180]  16'-7 3/8" [ 5064]  16'-8 1/4" [ 1884]  1-20 3" [80] MPT OVERFLOW	1'-3 1/4" [ 387 ]  (4) 1/2" [15]  FPT VENT		
	5'-11 3/4" [ 1822]	9 3/4" 9 9 1 ]		11'-11 3/4" [ 3651]	24'-2" [ 7366]  FACE A	1'-5" [ 432]
SHIPPING WEIGHT	36740 lbs+ [166	65] kg+	OPERATING 55700 lbs+ [25270] WEIGHT	D] kg+ HEAVIEST SECTION 15690 lbs+ [712	20] kg+ NO. OF SHIPPING SECTIONS 4	DRAWN BY: