UNIT	CLOSED CIRCUIT COOLER		EVADOO TNO EVEDED			DWG. # WB3TM2414-DRC-ST		REV.
MODEL #	ATWB 10-7L24	SCALE NTS	EVAPCO, INC. evapeo		SERIAL #		DATE _{11/21/2025}	
2. HÉAVI 3. MPT D FPT D BFW I GVD D FLG D PE DE 4. +UNIT ACCE: 5. MAKE 20 psi 6. *-APPI FOR F PIPING 7. 3/4" [1 RECO	AN MOTOR LOCATION PIEST SECTION IS UPPER S DENOTES MALE PIPE THRE DENOTES FEMALE PIPE TH DENOTES BEVELED FOR V DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END PRESSORIES (SEE ACCESSOF MIN [137 kPa], 50 psi MAX [PROXIMATE DIMENSIONS D PRE-FABRICATION OF CONG [9mm] DIA. MOUNTING HOL DIMMENDED STEEL SUPPOI NSIONS LISTED AS FOLLO ENGLISH FT-IN	EAD IREAD WELDING UDE RY DRAWINGS) [344 kPa] DO NOT USE INECTING LES. REFER TO RT DRAWING.	<u>P</u>	FACE B LAN VIEW	ACCESS DOOR FAC	CE A	ACCESS DOOR	FACE D
1	METRIC [mm] 4 [1 3'-11 3/4" * [1213] * (4) 4" [100] BFV (4) 4" [100] BFV (4) 4" [100] BFV (5) 2" [50] MPT MAKE-UP (4) 4" [100] BFV (5) 3" [80]	W FLUID OUT O	7" [178] 3/8" * 10'-5 1/8" [3180] 16'-7 3/8" [5064] 6'-2 1/4" [1884]	1'-3 1/4" [387] (4) 1/2" [15] FPT VENT				

SHIPPING WEIGHT 41120 lbs+ [18655] kg+ OPERATING WEIGHT 61400 lbs+ [27855] kg+ HEAVIEST SECTION WEIGHT 17880 lbs+ [8115] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR

1'-5" [432] - 11'-11 3/4" [3651]

> 24'-2" [7366]

FACE A

-(2) 3" [80] MPT OVERFLOW

FACE B