OOLING TOWER		EVADCO	INC. evapo	eo ®	DWG. #	CT4C071248-DRA-		REV
10DEL # AT 17-4H12	CALE NTS	EVAPCO,	TIAC:		SERIAL #			DATE 11/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SI 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDIN GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRA 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kF	ng Awings)	[1'-2" [356]	FACE B PLAN VIEW		FACE A	ACCESS DOOR	FACE I	<u>0</u>
1'-9 3/8" [543] 8" [200] BFW/GVD INLET		3'-8" 1118] - 2" [50] MPT	2'-11 3/8" [899]		M			
	" [80] MPT DVERFLOW 8" [200] BFW/GVD OUTLET 7'-4" [2235] -	3" [80] MPT DRAIN 4 1/4"	± 3/0, —	_	11'-11 3/4 [3651] FACE A	ł"		
SHIPPING 5390 lbs+ [2445] kg·	+ OPI	ERATING 8750 lbs+ [3970] kg+	HEAVIEST SECTION 3740	0 lbs+ [1700] kg+		SHIPPING SECTIONS	2 DR.	AWN BY: MBG