UNIT COOLING TOWER	EVADOO I		ap co °	DWG. #	CT4C071836-DRA-ST	REV	
MODEL # AT 17-3G18 SCALE NTS	EVAPCO, I			SERIAL #		DATE 12/13/2025	
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]		FACE B		FACE A	ACCESS D	FACE D	
1/ 	[356]	<u> </u>		- 1 -	- — 	Г	
1'-9 3/8" [543] 8" [200] BFW/GVD INLET	13'-4 [408	2'-11 3/8" [899] 5'-5 1/8" [1654] 2" 83]					
	2" [50] MPT 9'-3 3/4" [2837]	5'-1/4"					
3" [80] MPT — OVERFLOW — S" [200] — BFW/GVD OUTLET — 3'-1 3, [959	4 1/4" [107] 5 1/4" [132] 1'-9 1/4" [540] 3 5/8" [91]	1 3/8" [35]	-				
7'-4" [2235] ———————————————————————————————————		,	18'-0"				
SHIPPING 7910 lbs+ [3590] kg+ (3590] kg+	OPERATING 13040 lbs+ [5915] kg+	HEAVIEST SECTION WEIGHT	5280 lbs+ [2395] kg+	NO. OF SHI	PPING SECTIONS 2	RAWN BY: MBG	