COOLING TOWER	EVAPCO, INC. EVEPCO	DWG.# CT4C072836-DRA-ST REV -
AT 27-3J28 SCALE NTS	LVAPCO, INC.	SERIAL # DATE: 11/21/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]		FACE D FACE A FACE A
1'-9 3/8" [543] (2) 8" [200] BFW/GVD INLET	2'-11 3/8" [898] 2'-11 3/8" [898] 5'-5 1/8" [1654] 2) 2" [50] MPT 13'-10 3/4" [4235] 13'-10 3/4" [4235]	CCESS ACCESS ACCESS (MM)

5'-6 1/4" [1683]

1 3/8" [35]-

HEAVIEST SECTION WEIGHT <u>13</u>'-11 3/<u>4"</u>

[4261]

3860 lbs+ [1755] kg+

-2 1/2" [64]

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG

28'-2" [8585]

FACE A

(2) 3" [80] MPT DRAIN

> 1'-11 1/8" [587] 1'-2 7/8" [378]

19570 lbs+ [8880] kg+

^{_}7 1/2" [191]

_3 5/8" [92]

4 1/4"

[108]

5 1/4"

[133] ^{_3} 1'-9 1/4" [540]

3'-1 3/4"

[959]

OPERATING WEIGHT

7'-4" [2235] **FACE B**

(2) 3" [80] MPT OVERFLOW

(2) 8" [200] BFW/GVD

OUTLET

11720 lbs+ [5320] kg+

SHIPPING WEIGHT