UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 20-4K12	SCALE NTS


EVAPCO, INC. Evapco

DWG. # WB36M1208-DRC-ST REV. SERIAL # DATE\_11/16/2025


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]





**FACE A** 





SHIPPING WEIGHT 28940 lbs+ [13130] kg+ OPERATING WEIGHT

45280 lbs+ [20540] kg+

HEAVIEST SECTION WEIGHT

11910 lbs+ [5405] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: