UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 4-5G6





DWG. # REV. WB3040610-DRE-ST DATE 11/2/2025 SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]


FACE C


FACE B PLAN VIEW



FACE D

FACE A





DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 3570 lbs+ [1620] kg+ 5340 lbs+ [2425] kg+ 3060 lbs+ [1390] kg+ WEIGHT WEIGHT WEIGHT