UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 20-6J18

EVAPCO, INC. Evapco




DWG. # REV. WB36M1812-DRC-ST DATE<sub>11/14/2025</sub> SERIAL #


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

## FACE C



**FACE A** 





DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 22470 lbs+ [10195] kg+ 52280 lbs+ [23715] kg+ 80800 lbs+ [36655] kg+ WEIGHT WEIGHT WEIGHT