UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 9-6L12


EVAPCO, INC. Evapeo





DWG. # REV. WB3091212-DRC-ST SERIAL # DATE_{11/25/2025}

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







SHIPPING 14960 lbs+ [6790] kg+ WEIGHT

OPERATING WEIGHT

22080 lbs+ [10020] kg+

HEAVIEST SECTION WEIGHT

13160 lbs+ [5970] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR