


UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WB3091212-DRC-ST	REV.
MODEL #	ATWB 9-6M12	SCALE NTS		SERIAL #		DATE 1/12/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING WEIGHT 15010 lbs+ [6810] kg+ OPERATING WEIGHT 22130 lbs+ [10040] kg+ HEAVIEST SECTION WEIGHT 13210 lbs+ [5995] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR