UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 4-5G6-Z	SCALE NTS

EVAPCO, INC. Evapeo


OWG. #	WB3040610-DRE-SF	REV
SERIAL #		DATE 11/2/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] MM

FACE C


FACE B PLAN VIEW




FACE D

DRAWN BY: CAF

FACE A





NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 3570 lbs+ [1620] kg+ 5340 lbs+ [2425] kg+ 3060 lbs+ [1390] kg+ WEIGHT WEIGHT WEIGHT