

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. #		WB3091806-DRC-ST		REV.		-						
MODEL #		ATWB 9-3J18			SCALE		NTS		SERIAL #		DATE		10/19/2025				
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																	
FACE B PLAN VIEW					FACE C ACCESS DOOR ACCESS DOOR FACE D FACE A												
FACE B 1'-9 3/8" [543] 4'-3/4" [1238] 2'-2 3/8" [670] 6'-11 1/2" [2122] 11'-11 3/4" [3651] 1'-7 1/2" [495] 2" [50] MPT MAKE-UP 1'-11 1/8" [589] 3" [76] 2" [50] MPT DRAIN 5 1/4" [133] 4 1/4" [108] 5'-7 1/4" [1708] 8'-5 1/2" [2578] 2" [50] BFW 2" [50] BFW FLUID IN FLUID OUT 6" [154] 5'-1/4" [1529] 1'-3" [383] 3" [80] MPT OVERFLOW					FACE A 1'-7/8" [327] (2) 1/2" [15] FPT VENT 1'-5" [430] 18'-0" [5486]												
SHIPPING WEIGHT		15480 lbs+ [7025] kg+		OPERATING WEIGHT		23650 lbs+ [10730] kg+		HEAVIEST SECTION WEIGHT		12690 lbs+ [5760] kg+		NO. OF SHIPPING SECTIONS		2		DRAWN BY: SLR	