UNIT CLOSED CIRCUIT COOLER		OOLER	EVAPCO, INC. Evapeo		DWG. # WB3241408-DRC-ST	REV.
MODEL #	ATWB 24-4M14	SCALE NTS	EVAPCO, INC		SERIAL #	DATE _{11/10/2025}
2. HÉAVII 3. MPT D FPT DE BFW D GVD D FLG DI PE DEI 4. +UNIT ACCES 5. MAKE- 20 psi I 6. *-APPF FOR P PIPING 7. 3/4" [15 RECON	AN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THRI ENOTES FEMALE PIPE TH DENOTES BEVELED FOR V DENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCL SSORIES (SEE ACCESSOF UP WATER PRESSURE MIN [137 kPa], 50 psi MAX ROXIMATE DIMENSIONS D RE-FABRICATION OF CON DESTRUCTION OF	EAD IREAD VELDING UDE RY DRAWINGS) [344 kPa] IO NOT USE INECTING LES. REFER TO RT DRAWING.		FACE B PLAN VIEW	FACE A (2) ACCESS DOOR FACE FACE A	<u>.</u>
				7" 178] 1'-3 1/4" [387]		
	(4) 4* (4) 4*	[100] BFW FLUID IN FLUID OUT	5'-9.1/4" * 3'-3/8" * 9'-1/8" (2748) (4) 4' [100] BFW (4) 4' [100] BFW (5) (154] * [154] * 7'-2.1/4" (2189)	16'-2 3/8" [4937]		
	2'-1 1/4" [643] 3 5/8" 3 5/8" 92] (2) 3" [80] MPT OVERFLOW	(2) 2" [50] MPT — MAKE-UP (2) 3" [80] MPT DRAIN [130] — 24	11'-4 3/4" [3473] [11'-5" [433] [11'-5" [1422] [433] [11'-5" [1432] [433]	1'-6 1/2" -	13'-11 3/4"	
	1 -		7344] <u>CE B</u>		FACE A	