JNIT	CLOSED CIRCUIT COOLER	
10DEL #	ATWB 10-3I12-Z	SCALE NTS



DWG. # REV. WB3TM1206-DRC-SF DATE<sub>12/13/2025</sub> SERIAL #


**FACE D** 

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:


**ENGLISH FT-IN** METRIC [mm]

**FACE C** 



**FACE A** 





**SHIPPING** 12390 lbs+ [5625] kg+ WEIGHT

OPERATING WEIGHT

19900 lbs+ [9030] kg+

HEAVIEST SECTION WEIGHT

9840 lbs+ [4465] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: