UNIT	CLOSED CIRCUIT C	OOLER	FV/A DC/	O TNIC	TNIC evapeo		DWG. # WB3TM1808-DRC-SF	
MODEL #	ATWB 10-4L18-Z	SCALE NTS	<b>EVAPC</b>	J, INC.		SER	RIAL #	DATE 11/25/2025
2. HEAVIE 3. MPT DE FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT N ACCES 5. MAKE-I 20 psi N 6. *-APPR FOR PF PIPING 7. SERIES DRAIN 8. 3/4" [19 RECON 9. DIMEN:	N MOTOR LOCATION EST SECTION IS UPPER SE ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WI ENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SORIES (SEE ACCESSOR) UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 OXIMATE DIMENSIONS DO RE-FABRICATION OF CONN BY OTHERS. MMJ DIA. MOUNTING HOLE MMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW NGLISH FT-IN ETRIC [mm]	AD READ ELDING  DE Y DRAWINGS)  44 kPa] D NOT USE RECTING  CROSSOVER ES. REFER TO T DRAWING.	\[ \begin{align*} 7'' \ 178 \end{align*}	FAC PLAN VIE			ACE C  ACCESS DOOR  FACE A	FACE D
F	2" [50] MPT	3" [80] OVERFI	2'-6 3/8" * ['772] * 9'-1/8" ['2748]  (4) 4' [100] BFW ['2748]  FLUID OUT  14'-2 3/8" ['4328]  6" * 5'-2 1/4" ['1580]  1'-5" ['433]	SERIES FLOW PII (SEE NO AUX. CROSSOVER DI (SEE NO	rain		[18'-0" [5486]	
		I ACL D				<u>FAC</u>	<u> </u>	
SHIPPING WEIGHT	20640 lbs+ [9	365] kg+	OPERATING 32910 lbs+ [14930]	kg+ HEAVIEST S WEIG		6990 lbs+ [7710] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: